



# TL-D Standard Colours

## TL-D 58W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	4,000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V


Voltage (Nom)	111 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	68 kWh
Product Data	
Order product name	TL-D 58W/54-765 1SL/25
Full product name	TL-D 58W/54-765 1SL/25

TL-D Standard Colours

Full product code	871150095051240
Order code	251686
Material Nr. (12NC)	928049005422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500950512


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500950529

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	1-1/8 inch	59-1/16 inch	59-3/8 inch	59-1/4 inch	59-5/8 inch

Photometric data




Spectral Power Distribution Colour - TL-D 58W/54-765 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 58W/54-765 1SL/25



Life Expectancy Diagram - TL-D 58W/54-765 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 58W/54-765 1SL/25

