



# TL-D Standard Colours

## TL-D 58W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	13,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	4,000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V


Voltage (Nom)	111 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	68 kWh
Product Data	
Order product name	TL-D 58W/54-765 1SL/25
Full product name	TL-D 58W/54-765 1SL/25
Full product code	871150070275399

TL-D Standard Colours

Order code	928049005482
Material Nr. (12NC)	928049005482
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500702753


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500728234

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - TL-D 58W/54-765 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 58W/54-765 1SL/25



Life Expectancy Diagram - TL-D 58W/54-765 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 58W/54-765 1SL/25

