



# TUV T8

## TUV 55W HO 1SL/6

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

### 产品数据

基本資訊	
接口	G13 [ Medium Bi-Pin Fluorescent]
主要應用	Disinfection
可用使用時間 (標稱)	9000 h
系統說明	高輸出 (HO)
照明科技	
色碼	TUV
色彩名稱	- [ Not Specified]
可用使用時間下的流明衰減	10 %
運作和電氣	
Power (Rated) (Nom)	54 W
燈具電流 (標稱)	0.77 A
電壓 (標稱)	86 V
應用	
汞 (Hg) 含量 (標稱)	2.0 mg

紫外線	
UV-C 輻射	17.5 W
產品參數	
完整產品碼	871150061866510
訂購產品名稱	TUV 55W HO 1SL/6
EAN/UPC - 產品	8711500618665
訂購代碼	928049504003
分子 - 各件數量	1
分子 - 每一外盒內件數	6
材質編號(12NC)	928049504003
淨重 (件)	134.900 g


## TUV T8

### 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.


### 二维绘图

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 55W HO 1SL/6	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm




### TUV TL-D 55W HO

### 光度数据



XDPB\_XUTUVTLD-Spectral power distribution B/W



XDPO\_XUTUVTLD-Spectral power distribution Colour

