



MASTER CosmoWhite CPO-TT Xtra

MST CosmoWhite CPO-TT Xtra 315W/830 E40

New-generation ceramic metal-halide tubular lamps used in outdoor applications, offering efficient and pleasant white light

Warnings and Safety

- Use only in a totally enclosed luminaire, even during testing (IEC 61167, IEC 62035, IEC 60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with suitable electronic control gear
- Control gear must include end-of-life protection (IEC 61167, IEC 62035)
- E27 lamp holders and other parts in luminaires should be designed to withstand the ignition voltage of the electronic control gear (rated at 5 kV ignition pulse)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	30,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.426
Chromaticity Coordinate Y (Nom)	0.402
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	87


Arc Length O (Nom)	15.9 mm
Operating and Electrical	
Power Consumption	315.0 W
Voltage (Nom)	98 V
Voltage (Nom)	98 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

MASTER CosmoWhite CPO-TT Xtra

Bulb Shape	T46 [T 46mm]
Approval and Application	
Mercury (Hg) Content (Nom)	28.0 mg
Energy Consumption kWh/1000 h	347 kWh
Product Data	
Order product name	MST CosmoWhite CPO-TT Xtra 315W/830 E40
Full product name	MST CosmoWhite CPO-TT Xtra 315W/830 E40


Full product code	871869647753300
Order code	928061109227
Material Nr. (12NC)	928061109227
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696477533
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696477540

Dimensional drawing




Product	D (max)	D	O	L	C (max)
MST CosmoWhite CPO-TT Xtra 315W/830 E40	47 mm	46 mm	15.9 mm	162 mm	257 mm

Photometric data




Light Distribution Diagram - MST CosmoWhite CPO-TT Xtra 315W/830 E40



Spectral Power Distribution Colour - MST CosmoWhite CPO-TT Xtra 315W/830 E40

MASTER CosmoWhite CPO-TT Xtra

Lifetime



Life Expectancy Diagram - MST CosmoWhite CPO-TT Xtra 315W/830 E40

Lumen Maintenance Diagram - MST CosmoWhite CPO-TT Xtra 315W/830 E40

