



HPI-T High Wattage

HPI-T 2000W/646 E40 220V CRP/4

Quartz metal halide lamps with clear outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	E40	130 V	
Operating Position	P75 [Parallel +/-75D or Horizontal(HOR)]	Controls and Dimming	
Life to 50% Failures (Nom)	12,000 h	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	646 [CCT of 4600K]	Bulb Finish	Clear
Color Designation	Cool White (CW)	Bulb Shape	T100
Chromaticity Coordinate X (Nom)	375	Approval and Application	
Chromaticity Coordinate Y (Nom)	385	Mercury (Hg) Content (Nom)	155 mg
Correlated Color Temperature (Nom)	4200 K	Energy Consumption kWh/1000 h	2178 kWh
Luminous Efficacy (rated) (Nom)	95 lm/W	Product Data	
Color rendering index (CRI)	63	Order product name	HPI-T 2000W/646 E40 220V CRP/4
Arc Length O (Nom)	89 mm	Full product name	HPI-T 2000W/646 E40 220V CRP/4
Operating and Electrical		Full product code	871150018376745
Power Consumption	1,980 W	Local code description	HPIT2KW220VGES
Voltage (Nom)	130 V		

HPI-T High Wattage

Order code	928073609231
Material Nr. (12NC)	928073609231
Local order code	HPIT2KW220VGES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500183767


Numerator - Packs per outer box	4
EAN/UPC - Case	8711500183774

Dimensional drawing




Product	D (max)	O	L	C (max)
HPI-T 2000W/646 E40 220V CRP/4	101.5 mm	89 mm	290 mm	430 mm

Photometric data




Spectral Power Distribution Colour - HPI-T 2000W/646 E40 220V CRP/4

Lifetime



Life Expectancy Diagram - HPI-T 2000W/646 E40 220V CRP/4



Lumen Maintenance Diagram - HPI-T 2000W/646 E40 220V CRP/4

HPI-T High Wattage

