



# MASTERCoulour CDM-T

## MASTERC CDM-T 70W/830 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Light Technical	
Cap-Base	G12	Color Code	830 [CCT of 3000K]
Operating Position	UNIVERSAL [Any or Universal (U)]	Color Designation	Warm White (WW)
Life to 50% Failures (Nom)	12,000 hour(s)	Chromaticity Coordinate X (Nom)	0.432
		Chromaticity Coordinate Y (Nom)	0.395

# MASTERCoulour CDM-T

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	84
Arc Length O (Nom)	7 mm

## Operating and Electrical

Power Consumption	73.2 W
Voltage (Nom)	88 V
Voltage (Nom)	88 V

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T19


## Approval and Application

Mercury (Hg) Content (Nom)	4.6 mg
Energy Consumption kWh/1000 h	80 kWh

## Product Data



Order product name	MASTERC CDM-T 70W/830 G12 1CT/12
Full product name	MASTERC CDM-T 70W/830 G12 1CT/12
Full product code	871869648447000
Order code	928082305129
Material Nr. (12NC)	928082305129
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696484470
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696484487

## Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 70W/830 G12 1CT/12	20 mm	0.75 inch	7 mm	55 mm	57 mm	56 mm	103 mm

## Photometric data





Light Distribution Diagram - MASTERC CDM-T 70W/830 G12 1CT/12

Spectral Power Distribution Colour - MASTERC CDM-T 70W/830 G12 1CT/12

# MASTERC colour CDM-T

## Lifetime



Life Expectancy Diagram - MASTERC CDM-T 70W/830 G12 1CT/12

Lumen Maintenance Diagram - MASTERC CDM-T 70W/830 G12 1CT/12

