



MASTERC colour CDM-T 陶瓷複金屬燈

MASTERC CDM-T 150W/830 G12 1CT

精巧、高效率單端型放電式反射燈具系列，光色歷久如新，光線清晰明亮

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊		演色性指數 (CRI)		88
燈座基底	G12	電弧長 Ø (標稱)		9 mm
操作位置	UNIVERSAL [任何或通用 (U)]			
通量測量參考	Sphere	運轉與電力		
壽命 (故障率 50%) (標稱)	12,000 h	耗電量	150.1 W	
		電壓 (標稱)	96 V	
		電壓 (標稱)	96 V	
照明技術		控制與調光		
色碼	830 [CCT of 3000K]	可調光	否	
光通量	13,000 lm	機械與外罩		
色彩名稱	暖白光 (WW)	燈泡表層	透明	
色度坐標 X (標稱)	0.434			
色度坐標 Y (Nom)	0.398			
相關色彩溫度 (規範)	3000 K			
光效 (額定) (標準)	88 lm/W			

MASTERCoulour CDM-T 陶瓷複金屬燈

燈泡形狀	T19
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	14.3 mg
汞 (Hg) 含量 (標稱)	14.3 mg
能源消耗 kWh/1000 h	151 kWh
EPREL 註冊碼	473335
產品資料	
下訂產品名稱	MASTERC CDM-T 150W/830 G12 1CT


完整產品名稱	MASTERC CDM-T 150W/830 G12 1CT
完整產品代碼	871150019780115
訂單代碼	928083705125
材質 Nr. (12NC)	928083705125
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500197801
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500197818

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 in	9 mm	55 mm	57 mm	56 mm	110 mm

光度数据




Light Distribution Diagram - MASTERC CDM-T 150W/830 G12 1CT



Spectral Power Distribution Colour - MASTERC CDM-T 150W/830 G12 1CT

MASTERColour CDM-T 陶瓷複金屬燈

壽命



Life Expectancy Diagram - MASTERC CDM-T 150W/830 G12 1CT

Lumen Maintenance Diagram - MASTERC CDM-T 150W/830 G12 1CT

