



MASTERColour CDM-T

MASTERC CDM-T 150W/830 G12 1CT

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G12
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere

Life to 50% Failures (Nom)	12,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	13,000 lm

MASTERC colour CDM-T

Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.398
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	88
Arc Length O (Nom)	9 mm

Operating and Electrical

Power Consumption	150.1 W
Voltage (Nom)	96 V
Voltage (Nom)	96 V

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T19


Approval and Application

Energy Efficiency Class	G
Mercury (Hg) Content (Max)	14.3 mg
Mercury (Hg) Content (Nom)	14.3 mg
Energy Consumption kWh/1000 h	151 kWh
EPREL Registration Number	473335

Product Data


Order product name	MASTERC CDM-T 150W/830 G12 1CT
Full product name	MASTERC CDM-T 150W/830 G12 1CT
Full product code	871150019780115
Order code	928083705125
Material Nr. (12NC)	928083705125
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500197801
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500197818

Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 inch	9 mm	55 mm	57 mm	56 mm	110 mm

Photometric data





Light Distribution Diagram - MASTERC CDM-T 150W/830 G12 1CT



Spectral Power Distribution Colour - MASTERC CDM-T 150W/830 G12 1CT

MASTERCcolour CDM-T

Lifetime



Life Expectancy Diagram - MASTER CDM-T 150W/830 G12 1CT

Lumen Maintenance Diagram - MASTER CDM-T 150W/830 G12 1CT

