



CDM

CDM-SA/R 150W/942 UNP/1

Compact reflector discharge lamps with quartz outer bulb

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	CERAMICCAP-CABLE [Ceramic Cap-Cable (C)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	6,000 hour(s)
Light Technical	
Color Code	942 [CCT of 4200K]
Luminous Flux (Min)	2,295 lm
Luminous Flux	2,550 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.366
Chromaticity Coordinate Y (Nom)	0.353
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	16.1 lm/W
Color rendering index (CRI)	96
Operating and Electrical	
Power Consumption	158.0 W
Lamp Current (Nom)	1.76 A


Voltage (Nom)	106 V
Voltage (Nom)	106 V
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	CDM-SA/R 150W/942 UNP/1
Full product name	CDM-SA/R 150W/942 UNP/1
Full product code	871150020150800
Order code	928086805303
Material Nr. (12NC)	928086805303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900783490
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500201508

Dimensional drawing



Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	95.3 mm	280 mm	106 mm

Photometric data



Spectral Power Distribution Colour - CDM-SA/R 150W/942 UNP/1

