



CDM

CDM-SA/R 150W/942

The perfect color rendering and long life of these Ceramic Discharge Metal-halide lamps make them ideal for fiber optics lighting systems in shop displays, decorative lighting and swimming pool illumination. They can be mounted in color changing projectors.

Product data

General Information	
Base	CERAMICCAP-CABLE [Ceramic Cap-Cable (C)]
Operating Position	Universal [Universal]
Main Application	Fiber Optics
Life to 50% Failures (Nom)	6000 h
Light Technical	
Color Code	942 [CCT of 4200K]
Initial lumen (Min)	2200 lm
Initial lumen (Nom)	2650 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	366
Chromaticity Coordinate Y (Nom)	353
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	16.5 lm/W
Color Rendering Index (Nom)	96
Operating and Electrical	
Power (Rated) (Nom)	159 W
Lamp Current (Nom)	1.76 A
Ignition Supply Voltage (Min)	198 V


Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap-Base Information	Cable 250mm
Luminaire Design Requirements	
Bulb Temperature (Max)	650 °C
Pinch Temperature (Max)	350 °C
Product Data	
Order product name	CDM-SA/R 150W/942 UNP/1
EAN/UPC - Product	8727900783490
Order code	382788
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	928086805303
Net Weight (Piece)	0.192 kg

CDM

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Dimensional drawing




CDM-SA/R 150W/942

Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	95.3 mm	280 mm	106 mm

Photometric data



CDM-SA/R 150W/942



CDM-SA/R 150W/942

