



MASTERColour CDM-Tm 小型

MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12

单端小型陶瓷金属卤化物灯。PGJ5 扭锁光源灯座

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- For 20W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 20W
- For 35W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 35W
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底座	PGJ5
操作位置	UNIVERSAL [任意或通用 (U)]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	12,000 小时
灯技术	
颜色代码	830 [CCT of 3000K]
光通量	1,600 lm
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.434
色度坐标 Y (标称)	0.398
相关色温 (标称)	3000 K

光效 (额定) (标称)	72 lm/W
显色指数 (CRI)	87
弧长 Ø (标称)	3 mm
操作和电气	
功耗	22.1 W
电压 (标称)	100 V
电压 (标称)	100 V
控制和调光	
可调光	否

MASTERC colour CDM-Tm 小型

机械和外壳	
灯泡外观	透明
灯泡外形	T13.3 [T 13.3 毫米]
审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	2.4 mg
汞 (Hg) 含量 (标称)	2.4 mg
能耗 kWh/1000 h	23 kWh
EPREL 注册号	473347
产品数据	
订单产品名称	MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12


二维绘图




完整的产品名称	MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12
完整产品代码	87115002075175
订购代码	928087905130
材料编号 (12NC)	928087905130
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500207517
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8711500207524

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12	13.2 mm	0.44 in	3 mm	22.3 mm	22.9 mm	22.6 mm	52 mm

光度数据




Light Distribution Diagram - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12




Spectral Power Distribution Colour - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12

MASTERC colour CDM-Tm 小型

寿命



Life Expectancy Diagram - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12



Lumen Maintenance Diagram - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12

