



MASTERColour CDM-TC

MASTERColour CDM-TC 35W/842 G8.5 1CT/12

Range of single-ended, very compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

Product data

General Information		Color Rendering Index (Nom)	
Cap-Base	G8.5 [G8.5]		85
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 5% Failures (Nom)	6000 h	Power (Rated) (Min)	39.0 W
Life To 10% Failures (Nom)	8000 h	Power (Nom)	39.1 W
Life to 20% Failures (Nom)	9000 h	Ignition Supply Voltage (Max)	198 V
Life to 50% Failures (Nom)	12000 h	Ignition Supply Voltage (Min)	198 V
ANSI Code HID	-	Re-Ignition Time (Min) (Max)	15 min
Light Technical		Ignition Time (Max)	30 s
Color Code	842 [CCT of 4200K]	Voltage (Max)	93 V
Luminous Flux (Rated) (Nom)	3100 lm	Voltage (Min)	77 V
Color Designation	Cool White (CW)	Voltage (Nom)	85 V
Lumen Maintenance 10000 h (Nom)	70 %	Controls and Dimming	
Lumen Maintenance 2000 h (Min)	75 %	Dimmable	No
Lumen Maintenance 2000 h (Nom)	85 %	Run-Up Time 90% (Max)	3 min
Lumen Maintenance 5000 h (Min)	70 %	Mechanical and Housing	
Lumen Maintenance 5000 h (Nom)	80 %	Bulb Finish	Clear
Chromaticity Coordinate X (Nom)	0.374	Bulb Material	UV-Block Quartz
Chromaticity Coordinate Y (Nom)	0.369		
Correlated Color Temperature (Nom)	4200 K		
Luminous Efficacy (rated) (Nom)	79 lm/W		

MASTERCcolour CDM-TC

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.7 mg
Energy Consumption kWh/1000 h	43 kWh

UV

Pet (Niosh) (Min)	8 h/500lx
Damage Factor D/fc (Max)	0.5


Luminaire Design Requirements

Bulb Temperature (Max)	500 °C
Pinch Temperature (Max)	300 °C

Product Data

Full product code	871150020957315
Order product name	MASTERCcolour CDM-TC 35W/842 G8.5 1CT/12
EAN/UPC - Product	8711500209573
Order code	928093805125
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928093805125
Net Weight (Piece)	10.000 g
ILCOS Code	MT/UB-35/842-H-G8.5-17/85

Dimensional drawing



CDM-TC 35W/842 G8.5

Product


MASTERCcolour CDM-TC 35W/842 G8.5 1CT/12

Photometric data



MASTERCcolour CDM-TC

Lifetime



LDLE_CDM-TC_0001-Life expectancy diagram

