



MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12

微型單端陶瓷複金屬燈。PGJ5 型一旋即緊燈座

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- For 20W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 20W
- For 35W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 35W
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊			
燈座基底	PGJ5 [PGJ5]	色度坐標 X (標稱)	0.434
操作位置	UNIVERSAL [任何或通用 (U)]	色度坐標 Y (Nom)	0.398
通量測量參考	Sphere	相關色彩溫度 (規範)	3000 K
壽命 (故障率 50 %) (標稱)	12,000 h	光效 (額定) (標準)	77 lm/W
		演色性指數 (CRI)	91
		電弧長 O (標稱)	4 mm
照明技術		運轉與電力	
色碼	930 [CCT of 3000K]	耗電量	39.1 W
光通量	3,000 lm	電壓 (標稱)	96 V
色彩名稱	暖白光 (WW)		

MASTERCoulour CDM-Tm Mini 小型陶瓷複金屬燈

電壓 (標稱)	96 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	T13.3 [T 13.3mm]
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	2.7 mg
汞 (Hg) 含量 (標稱)	2.74 mg
能源消耗 kWh/1000 h	40 kWh


EPREL 註冊碼	473353
產品資料	
下訂產品名稱	MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12
完整產品名稱	MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12
完整產品代碼	871150021149115
訂單代碼	928093905130
材質 Nr. (12NC)	928093905130
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500211491
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500211507

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12	13.2 mm	0.44 in	4 mm	22.3 mm	22.9 mm	22.6 mm	52 mm

光度数据




Light Distribution Diagram - MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12




Spectral Power Distribution Colour

MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

壽命



Life Expectancy Diagram - MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12



Lumen Maintenance Diagram

