



# MASTERColour CDM-T

## MASTERColour CDM-T 250W/942 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

### Product data

General Information	
Cap base	G12 [ G12]
Operating position	UNIVERSAL [ Any/Universal]
Life to 5% failures (nom.)	3500 h
Life to 10% failures (nom.)	10000 h
Life to 20% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
ANSI code HID	-
Light Technical	
Colour code	942 [ CCT of 4,200 K]
Luminous flux (rated) (min.)	23400 lm
Luminous flux (rated) (nom.)	26000 lm
Colour designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	86 %
Lumen maintenance 2,000 hours (nom.)	98 %
Lumen maintenance 5,000 hours (nom.)	94 %
Chromaticity coordinate X (nom.)	0.376
Chromaticity coordinate Y (nom.)	0.368
Correlated colour temperature (nom.)	4200 K
Luminous efficacy (rated) (nom.)	105 lm/W
Color rendering index (nom.)	91

Ratio Scotopic/Photopic Lumens	1.75
Operating and Electrical	
Power (Rated) (Nom)	247 W
Lamp current run-up (max.)	6 A
Lamp current (EM) (nom.)	3.04 A
Ignition supply voltage (max.)	198 V
Ignition peak voltage (max.)	5000 V
Ignition supply voltage (min.)	198 V
Ignition peak voltage (min.)	3500 V
Re-ignition time (min.) (max.)	15 min
Ignition time (max.)	30 s
Voltage (Max)	104 V
Voltage (Min)	84 V
Voltage (Nom)	93 V
Controls and Dimming	
Dimmable	no
Run-up time 90% (max.)	3 min

# MASTERCcolour CDM-T


Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	20.0 mg
Energy Consumption kWh/1000 h	272 kWh
UV	
PET (NIOSH) (min.)	8 h/500lx
Damage factor D/fc (nom.)	0.28
Luminaire Design Requirements	
Bulb temperature (max.)	700 °C
Cap base temperature (max.)	280 °C

Pinch temperature (max.)	350 °C
Product Data	
Full product code	871150021112515
Order product name	MASTERCcolour CDM-T 250W/942 G12 1CT/12
EAN/UPC – product	8711500211125
Order code	21112515
Local Code	250CDMT942
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	928094205131
Net weight (piece)	0.039 kg
ILCOS Code	MT/UB-250/942-H-G12-25/135

## Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Dimensional drawing




CDM-T 250W/942 G12

Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERCcolour CDM-T	25 mm	12.3	71.5 mm	73.5 mm	72.5	135 mm
250W/942 G12 1CT/12		mm			mm	

# MASTERCoulour CDM-T

## Photometric data



## Lifetime

