



MASTERCcolour CDM-T

MASTERCcolour CDM-T 35W/842 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information			
Cap-Base	G12 [G12]	Lumen Maintenance 10000 h (Nom)	70 %
Operating Position	UNIVERSAL [Any or Universal (U)]	Lumen Maintenance 2000 h (Min)	80 %
Life to 5% Failures (Nom)	9000 h	Lumen Maintenance 2000 h (Nom)	90 %
Life To 10% Failures (Nom)	10000 h	Lumen Maintenance 5000 h (Min)	75 %
Life to 20% Failures (Nom)	11000 h	Lumen Maintenance 5000 h (Nom)	85 %
Life to 50% Failures (Nom)	12000 h	Chromaticity Coordinate X (Nom)	0.370
ANSI Code HID	-	Chromaticity Coordinate Y (Nom)	0.367
		Correlated Color Temperature (Nom)	4200 K
		Luminous Efficacy (rated) (Nom)	77 lm/W
		Color Rendering Index (Nom)	84
Light technical		Operating and electrical	
Color Code	842 [CCT of 4200K]	Power (Nom)	39.1 W
Luminous Flux (Rated) (Nom)	3000 lm		
Color Designation	Cool White (CW)		

MASTERCcolour CDM-T

Lamp Current Run-Up (Max)	0.720 A
Ignition Supply Voltage (Max)	198 V
Ignition Peak Voltage (Max)	5000 V
Ignition Supply Voltage (Min)	198 V
Ignition Peak Voltage (Min)	3500 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	30 s
Voltage (Max)	93 V
Voltage (Min)	77 V
Voltage (Nom)	85 V

Controls and dimming

Dimmable	No
Run-Up Time 90% (Max)	3 min

Mechanical and housing

Bulb Finish	Clear
Bulb Shape	T19 [T 19mm]

Approval and application

Mercury (Hg) Content (Nom)	2.7 mg
Energy Consumption kWh/1000 h	43 kWh

UV

Pet (Niosh) (Min)	8 h/500lx
Damage Factor D/fc (Max)	0.5


Luminaire design requirements

Bulb Temperature (Max)	500 °C
Cap-Base Temperature (Max)	280 °C
Pinch Temperature (Max)	350 °C

Product data

Full product code	871869648445600
Order product name	MASTERCcolour CDM-T 35W/842 G12 1CT/12
EAN/UPC - Product	8718696484456
Order code	928094305129
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928094305129
Net Weight (Piece)	28.000 g
ILCOS Code	MT/UB-35/842-H-G12-20/90

Dimensional drawing




MASTERCcolour CDM-T 35W/842 G12 1CT/12

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERCcolour CDM-T 35W/842 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56	103 mm
							mm








MASTERCoulour CDM-T

Photometric data



LDLD_CDM-T_0001-Light distribution diagram

LDLD_CDM-T_0002-Light distribution diagram




LDLD_CDM-T_0005-Light distribution diagram

LDPO_CDM-T_35W_842-Spectral power distribution Colour

MASTERCcolour CDM-T

Lifetime



LDLE_CDM-T_0001-Life expectancy diagram

