



# Architectural MSD

## MSD 575 HR 1CT/8

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information	
Cap-Base	G22
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	47,000 lm
Chromaticity Coordinate X (Nom)	328
Chromaticity Coordinate Y (Nom)	331
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	81 lm/W
Color rendering index (CRI)	75
Arc Length O (Nom)	8.0 mm

Operating and Electrical	
Power Consumption	575 W
Lamp Current (Nom)	6.95 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD 575 HR 1CT/8
Full product name	MSD 575 HR 1CT/8
Full product code	872790091648500
Order code	245472
Material Nr. (12NC)	928098905114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900916485

Architectural MSD


Numerator - Packs per outer box	8
EAN/UPC - Case	8727900916492

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 575	1-3/16	5/16	2-3/4	2-13/16	2-3/4	5-3/4	1-3/4	1-11/16	1-5/8
HR 1CT/8	inch	inch	inch	inch	inch	inch	inch	inch	inch

Photometric data



Spectral Power Distribution Colour - MSD 575 HR 1CT/8

