



MSR Gold™ SA Double Ended

MSR GOLD 1200 SA/DE UNP/108

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	SFC10-4 [SFC10-4]		85
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	7.0 mm
Life to 50% Failures (Nom)	750 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	1,200 W
Color Code	- [Not Specified]	Lamp Current (Nom)	13.6 A
Luminous Flux	103,000 lm	Controls and Dimming	
Chromaticity Coordinate X (Nom)	326	Dimmable	No
Chromaticity Coordinate Y (Nom)	332	Product Data	
Correlated Color Temperature (Nom)	6000 K	Order product name	MSR Gold 1200 SA/DE UNP/108
Luminous Efficacy (Rated) (Min)	77 lm/W	Full product name	MSR GOLD 1200 SA/DE UNP/108
Luminous Efficacy (rated) (Nom)	86 lm/W		

MSR Gold™ SA Double Ended

Full product code	87115002071129
Order code	20711129
Material Nr. (12NC)	928099605112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500207111


Numerator - Packs per outer box	108
EAN/UPC - Case	8711500206909

Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold 1200 SA/DE UNP/108	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 1200 SA/DE UNP/108

