



# MSR Gold™ SA Double Ended

## MSR Gold™ 1200 SA/DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


<b>General Information</b>		<b>Color rendering index (CRI)</b>		83
Cap-Base	SFC10-4 [SFC10-4]	<b>Operating and Electrical</b>		
Operating Position	UNIVERSAL [Any or Universal (U)]	Power Consumption	1,200 W	
<b>Light Technical</b>		Lamp Current (Nom)	13.6 A	
Color Code	- [Not Specified]	<b>Controls and Dimming</b>		
Luminous Flux	103,000 lumen	Dimmable	No	
Chromaticity Coordinate X (Nom)	326	<b>Product Data</b>		
Chromaticity Coordinate Y (Nom)	332	Full product code	871829122121000	
Correlated Color Temperature (Nom)	6000 K	Order product name	MSR Gold 1200 SA/DE 1CT/4	
Luminous Efficacy (Rated) (Min)	77 lm/W	Order code	22121000	
Luminous Efficacy (rated) (Nom)	86 lm/W			

# MSR Gold™ SA Double Ended

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material number (12NC)	928099605115
Full product name	MSR Gold™ 1200 SA/DE 1CT/4


EAN/UPC - Case	8718291221227
----------------	---------------

## Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

## Photometric data



Spectral Power Distribution Colour - MSR Gold 1200 SA/DE 1CT/4

