



MSR Hot Restrike

MSR 1200 HR 1CT/2

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G38
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,000 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	103,000 lm
Chromaticity Coordinate X (Nom)	323
Chromaticity Coordinate Y (Nom)	328
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (Rated) (Min)	75 lm/W
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	95
Arc Length O (Nom)	10.0 mm

Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	13.5 A
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR 1200 HR 1CT/2
Full product name	MSR 1200 HR 1CT/2
Full product code	872790092606400
Order code	92606400
Material Nr. (12NC)	928105005114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900926064
Numerator - Packs per outer box	2

MSR Hot Restrike


EAN/UPC - Case	8727900926071
----------------	---------------

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 1200	40 mm	10.0	106	108 mm	107	200	67 mm	65	63 mm
HR 1CT/2		mm	mm		mm	mm		mm	

Photometric data



Spectral Power Distribution Colour - MSR 1200 HR 1CT/2

