



# MSR Gold™ FastFit

## MSR Gold™ 2000/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information		Correlated Colour Temperature (Nom)	
Cap base	PGJX50 [ PGJX50]		7500 K
Operating position	UNIVERSAL [ Any or Universal (U)]	Luminous efficacy (rated) (nom.)	78 lm/W
Main application	Entertainment	Colour rendering index (nom.)	88
Life to 50% failures (nom.)	750 h	<b>Operating and electrical</b>	
System description	FastFit	Power (Rated) (Nom)	2000 W
<b>Light technical</b>		Lamp current (nom.)	15.4 A
Colour Code	2	Ignition supply voltage (min.)	198 V
Luminous flux (nom.)	157000 lm	<b>Controls and dimming</b>	
Chromaticity coordinate X (nom.)	297	Dimmable	Yes
Chromaticity coordinate Y (nom.)	322		

# MSR Gold™ FastFit

## Mechanical and housing

Cap-base information PGJX50

## Luminaire design requirements

Bulb temperature (max.) 950 °C

Pinch temperature (max.) 500 °C

Pinch Temperature (Max)-DUP(do not use) 500 °C

## Product data

Full product code 872790090830500

Order product name MSR Gold™ 2000/2 FastFit 1CT/8

EAN/UPC – product 8727900908305

Order code 90830500

SAP numerator – quantity per pack 1

Numerator – packs per outer box 8

SAP material 928106105114

Net Weight (Piece) 0.147 g

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 2000/2 FastFit 1CT/8	34 mm	8.0 mm	66 mm	68 mm	67 mm	134 mm	50 mm

MSR Gold™ 2000/2 FastFit 1CT/8

