



MSR Gold™ FastFit

MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Mises en garde et sécurité

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Données du produit


Renseignements généraux		Indice de rendu des couleurs (IRC)	
Culot-Base	PGJX50 [PGJX50]		73
Position de fonctionnement	UNIVERSEL [Tous ou universel (U)]	Longueur de l'arc O (nominal)	3,8 mm
Durée de vie jusqu'à 50% des défaillances (nom.)	750 h	Fonctionnement et électricité	
Données techniques sur l'éclairage		Consommation	700 W
Code de couleur	2	Courant de la lampe (nom.)	10,2 A
Flux lumineux	48 000 lm	Commandes et gradation	
Coordonnée de chromaticité X (nominale)	298	Intensité variable	Oui
Coordonnée de chromaticité Y (nominale)	322	Données de produit	
Température de couleur proximale (nom.)	7500 K	Nom du produit de la commande	MSR Gold 700/2 FastFit 1CT/8
Efficacité lumineuse (nominale)	68 lm/W		

MSR Gold™ FastFit

Nom complet du produit	MSR Gold™ 700/2 FastFit 1CT/8
Full EOC	872790090850300
Code de commande	245621
Numéro de matériau (12 N.C.)	928106205114
Numérateur – Quantité par emballage	1


EAN/CUP – Produit/Boîtier	8727900908503
Numérateur – Emballages par boîte extérieure	8
EAN/CUP – Boîte	8727900908510

Schéma dimensionnel



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 700/2 FastFit 1CT/8	23,2 mm	3,8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

Données photométriques



Spectral Power Distribution Colour – MSR Gold 700/2 FastFit 1CT/8

