



MASTERCcolour CDM-R Elite

MASTERCcolour CDM-R Elite 35W/930 E27 PAR30L 30D

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

Product data

General Information	
Cap base	E27 [E27]
Burning Position	UNIVERSAL [Any/Universal]
Life to 5% failures (nom.)	9000 h
Life to 10% failures (nom.)	5500 h
Life to 20% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
Switching cycle	1350X

Light Technical	
Colour Code	930 [CCT of 3,000 K]
Technical Beam Angle (Nom)	30 °
Beam angle technical	30 °
Luminous intensity (nom.)	8000 cd
Beam description	Flood [Flood]
Colour Designation	Warm white (WW)
Lumen maintenance 12,000 hours (nom.)	82 %
Lumen maintenance 2,000 hours (nom.)	94 %
Lumen maintenance 4,000 hours (nom.)	90 %
Design mean lumens	2000 lm
Chromaticity coordinate X (nom.)	0.437

Chromaticity coordinate Y (nom.)	0.400
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	69 lm/W
Colour Rendering Index,horiz (Min)	88
Colour Rendering Index,horiz (Nom)	91
LLMF at end of nominal lifetime (nom.)	80 %
Luminous Flux in 90° Cone (Rated)	2400 lm

Operating and Electrical	
Power (Rated) (Nom)	39 W
Lamp current (EM) (nom.)	0.450 A
Ignition supply voltage (min.)	198 V
Re-ignition time (min.) (max.)	15 min
Warm-up time to 60% light (nom.)	120 s
Ignition time (max.)	30 s
Voltage (Max)	96 V
Voltage (Min)	80 V
Voltage (Nom)	88 V

Controls and Dimming	
Dimmable	no

MASTERCLOUR CDM-R Elite


Run-up time 90% (max.)	3 min
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4.7 mg
Energy Consumption kWh/1000 h	43 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	300 °C
Cap base temperature (max.)	200 °C

Product Data	
Full product code	871829124194200
Order product name	MASTERCLOUR CDM-R Elite 35W/930 E27 PAR30L 30D
EAN/UPC – product	8718291241942
Order code	24194200
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	928108200630
Net weight (piece)	0.220 kg
ILCOS Code	MRS/UB-35/930-H-E27-95/125/30

Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)



Dimensional drawing



CDM-R Elite 35W/930 E27 PAR30L 30D

Product	D (max)	C (max)
MASTERCLOUR CDM-R Elite 35W/930 E27 PAR30L 30D	97 mm	123 mm

Photometric data



MASTERCcolour CDM-R Elite

Lifetime

