



MasterColor CDM-R Elite

MC CDM-R Elite 70W/930 E26 PAR30L 40D

The Elite family is at the very top of the MasterColor CDM range, and gives a unique combination of unbeatable light quality and consistent performance over lifetime, while keeping running costs low. MasterColor metal halide lamps deliver consistent white light and higher color rendering than any standard metal halide source for architectural lighting.MasterColor CDM Elite PAR30L lamps deliver similar performance as the MasterColor Elite family lamps in the familiar PAR30L shape.

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information		
Cap-Base	E26 [Single Contact Medium Screw]	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Switching Cycle	1,350	
Life to 50% Failures (Nom)	15,000 hour(s)	
Light Technical		
Color Code	930 [CCT of 3000K]	
Beam Angle (Nom)	40 degree(s)	
Luminous Intensity (Nom)	9,300 cd	
Color Designation	Warm White (WW)	
Chromaticity Coordinate X (Nom)	0.443	

Chromaticity Coordinate Y (Nom)	0.402
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color rendering index (CRI)	92
LLMF At End Of Nominal Lifetime (Nom)	80 %
Luminous Flux in 90° Cone (Rated)	4,400 lm
Operating and Electrical	
Power Consumption	73.0 W
Warm-up time to 60% light	120 s
Voltage (Nom)	86 V


Datasheet, 2023, November 30 data subject to change

MasterColor CDM-R Elite

Voltage (Nom)	86 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	PAR30L
Approval and Application	
Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	80 kWh
· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·


MC CDM-R Elite 70W/930 E26 PAR30L 40I	
MC CDM-R Elite 70W/930 E26 PAR30L 40I	
928109800615	
928109800615	
1	
046677426545	
6	
50046677426540	

Dimensional drawing




Product	D (max)	C (max)
MC CDM-R Elite 70W/930 E26 PAR30L 40D	97 mm	123 mm

Photometric data




Light Distribution Diagram - MC CDM-R Elite 70W/930 E26 PAR30L 40D




Spectral Power Distribution Colour - MC CDM-R Elite 70W/930 E26 PAR30L 40D

MasterColor CDM-R Elite

Lifetime





Life Expectancy Diagram - MC CDM-R Elite 70W/930 E26 PAR30L 40D

Lumen Maintenance Diagram - MC CDM-R Elite 70W/930 E26 PAR30L 40D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.