



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold 1000 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	PGJX36	Luminous Efficacy (rated) (Nom)	82 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	80
Life to 50% Failures (Nom)	900 hour(s)	Arc Length O (Nom)	5.5 mm
Light Technical		Controls and Dimming	
Color Code	- [Not Specified]	Power Consumption	1,000.0 W
Luminous Flux	82,000 lm	Lamp Current (Nom)	11.4 A
Chromaticity Coordinate X (Nom)	0.321	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	0.330		
Correlated Color Temperature (Nom)	6000 K		

MSR Gold™ MiniFastFit (Touring/Stage)

Product Data	
Order product name	MSR Gold 1000 MiniFastFit 1CT/4
Full product name	MSR Gold 1000 MiniFastFit 1CT/4
Full product code	871829178508800
Order code	928171405115
Material Nr. (12NC)	928171405115

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291785088
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291785095

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 1000 MiniFastFit 1CT/4	26 mm	5.5 mm	55 mm	57 mm	56	112 mm	36.5 mm	36 mm	35.3 mm

