



# MSR

## MSR 700/2 1CT/8

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.


### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


| General Information                |                                  | Lamp Current (Nom)              |                 |
|------------------------------------|----------------------------------|---------------------------------|-----------------|
| Cap-Base                           | G22 [G22]                        |                                 | 11 A            |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] | Controls and Dimming            |                 |
|                                    |                                  | Dimmable                        | No              |
| Light Technical                    |                                  | Product Data                    |                 |
| Color Code                         | 2                                | Full product code               | 872790091638600 |
| Luminous Flux                      | 55,000 lumen                     | Order product name              | MSR 700/2 1CT/8 |
| Chromaticity Coordinate X (Nom)    | 302                              | Order code                      | 91638600        |
| Chromaticity Coordinate Y (Nom)    | 320                              | Numerator - Quantity Per Pack   | 1               |
| Correlated Color Temperature (Nom) | 7200 K                           | Numerator - Packs per outer box | 8               |
| Luminous Efficacy (rated) (Nom)    | 78 lm/W                          | Material number (12NC)          | 928171505114    |
| Color rendering index (CRI)        | 80                               | Full product name               | MSR 700/2 1CT/8 |
| Operating and Electrical           |                                  | EAN/UPC - Case                  | 8727900916393   |
| Power Consumption                  | 700 W                            |                                 |                 |

Dimensional drawing



| Product         | D (max) | O      | L (min) | L (max) | L     | C (max) | F     |
|-----------------|---------|--------|---------|---------|-------|---------|-------|
| MSR 700/2 1CT/8 | 30 mm   | 8.0 mm | 74 mm   | 76 mm   | 75 mm | 152 mm  | 42 mm |

Photometric data



Spectral Power Distribution Colour - MSR 700/2 1CT/8

