



MSR

MSR 1200/2.1CT/3

MSR – bright vivid colours, always The high colour rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colours of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G22
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	800 h
Light Technical	
Color Code	2
Luminous Flux	104,000 lm
Chromaticity Coordinate X (Nom)	302
Chromaticity Coordinate Y (Nom)	320
Correlated Color Temperature (Nom)	7200 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	85

Arc Length O (Nom)	10.0 mm
Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	13.8 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSR 1200/2.1CT/3
Full product name	MSR 1200/2.1CT/3
Full product code	872790091133600
Local code description	MSR12002

Order code	928171805114
Material Nr. (12NC)	928171805114
Local order code	MSR12002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900911336


Numerator - Packs per outer box	3
EAN/UPC - Case	8727900911343

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200/2.1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm

Photometric data



Spectral Power Distribution Colour - MSR 1200/2.1CT/3

