



Architectural MSD

MSD 1200.1CT/3

Architectural MSD – single ended night colours The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent colour rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	G22 [G22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	92,000 lm
Chromaticity Coordinate X (Nom)	323
Chromaticity Coordinate Y (Nom)	328
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	79 lm/W
Color rendering index (CRI)	73
Arc Length O (Nom)	14.0 mm
Operating and Electrical	
Power Consumption	1,200 W

Lamp Current (Nom)	13.8 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD 1200.1CT/3
Full product name	MSD 1200.1CT/3
Full product code	872790091135000
Order code	928172005114
Material Nr. (12NC)	928172005114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900911350
Numerator - Packs per outer box	3
EAN/UPC - Case	8727900911367


Architectural MSD

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD	42.5	14.0	84 mm	86 mm	85	183 mm	54 mm	53	52 mm
1200.1CT/3	mm	mm			mm			mm	

Photometric data



Spectral Power Distribution Colour – MSD 1200.1CT/3

