



# MSR Gold™ SA Double Ended

## MSR Gold 1200 SA/2 DE UNP/108

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

### 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般信息	
底座	SFC10-4 [SFC10-4]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	750 小时

灯技术	
颜色代码	- [Not Specified]
光通量	100,000 lm
色度坐标 X (标称)	301
色度坐标 Y (标称)	316
相关色温 (标称)	7500 K
光效 (额定)(最低)	75 lm/W
光效 (额定)(标称)	83 lm/W

显色指数 (CRI)	85
弧长 O (标称)	7.0 mm

操作和电气	
功耗	1,200 W
灯具电流 (标称)	13.6 A

控制和调光	
可调光	否


产品数据	
订单产品名称	MSR Gold 1200 SA/2 DE UNP/108
完整的产品名称	MSR Gold 1200 SA/2 DE UNP/108

## MSR Gold™ SA Double Ended

完整产品代码	871150020899629
订购代码	928175305112
材料编号 (12NC)	928175305112
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500208996


计算器 - 每个外包装箱中的包数	108
EAN/UPC - 案例	8711500209009

### 二维绘图



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold 1200 SA/2 DE UNP/108	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

### 光度数据



Spectral Power Distribution Colour - MSR Gold 1200 SA/2 DE UNP/108

