



MSR Gold™ SA Double Ended

MSR Gold™ 1200 SA/2 DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Product data

General Information		Operating and Electrical	
Base	SFC10-4 [SFC10-4]	Power (Rated) (Nom)	1200 W
Operating Position	Universal [Universal]	Lamp Current (Nom)	13.6 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life to 50% Failures (Nom)	750 h		
System Description	SA/2 DE		
Light Technical		Controls and Dimming	
Color Code	- [Not Specified]	Dimmable	No
Initial lumen (Min)	90000 lm		
Initial lumen (Nom)	100000 lm	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	301	Cap-Base Information	SFC10-4
Chromaticity Coordinate Y (Nom)	316		
Correlated Color Temperature (Nom)	7500 K	Product Data	
Luminous Efficacy (Rated) (Min)	75 lm/W	Order product name	MSR Gold™ 1200 SA/2 DE 1CT/4
Luminous Efficacy (rated) (Nom)	83 lm/W	EAN/UPC - Product	8718291221074
Color Rendering Index (Nom)	85	Order code	287250
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	4
		Material Nr. (12NC)	928175305115


MSR Gold™ SA Double Ended

Net Weight (Piece) 34.000 g

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold™ 1200 SA/2 DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

MSR GOLD 1200 SA/2 DE

Photometric data



MSR Gold™ 1200 SA/2 DE

MSR Gold™ 1200 SA/2 DE

