



# MSR Gold™ MiniFastFit (DJ/Club)

## MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Product data

General Information	
Cap base	PGJX28 [ PGJX28]
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Entertainment
Life to 50% failures (nom.)	750 h
System description	MiniFastFit
Light Technical	
Colour code	2
Luminous flux (min.)	19170 lm
Luminous flux (nom.)	21300 lm
Chromaticity coordinate X (nom.)	288
Chromaticity coordinate Y (nom.)	306
Correlated colour temperature (nom.)	9300 K
Luminous efficacy (rated) (min.)	64 lm/W
Luminous efficacy (rated) (nom.)	71 lm/W
Color rendering index (nom.)	80

Operating and Electrical	
Power (Rated) (Nom)	300 W
Lamp current (nom.)	3.75 A
Ignition supply voltage (min.)	207 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap base information	PGJX28
Luminaire Design Requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	500 °C
Product Data	
Full product code	871829122111100
Order product name	MSR Gold™ 300/2 MiniFastFit 1CT/4

## MSR Gold™ MiniFastFit (DJ/Club)


EAN/UPC – product	8718291221111
Order code	22111100
Numerator – quantity per pack	1
Numerator – packs per outer box	4

Material no. (12NC)	928177105115
Net weight (piece)	0.062 kg

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm
MiniFastFit 1CT/4						

MSR GOLD 300/2 MiniFastFit

