



MSR Gold™ MiniFastFit (DJ/club)

MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Mises en garde et sécurité

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Données du produit

Renseignements généraux	
Culot-Base	PGJX28 [PGJX28]
Position de fonctionnement	UNIVERSEL [Tous ou universel (U)]
Durée de vie jusqu'à 50% des défaillances (nom.)	750 h
Données techniques sur l'éclairage	
Code de couleur	2
Flux lumineux	22 700 lm
Coordonnée de chromaticité X (nominale)	288
Coordonnée de chromaticité Y (nominale)	306
Température de couleur proximale (nom.)	9300 K
Efficacité lumineuse (nominale) (min.)	64 lm/W
Efficacité lumineuse (nominale)	75 lm/W


Indice de rendu des couleurs (IRC)	78
Longueur de l'arc O (nominal)	5,0 mm
Fonctionnement et électricité	
Consommation	300 W
Courant de la lampe (nom.)	3,75 A
Commandes et gradation	
Intensité variable	Oui
Données de produit	
Nom du produit de la commande	MSR Gold 300/2 MiniFastFit 1CT/4
Nom complet du produit	MSR Gold™ 300/2 MiniFastFit 1CT/4

MSR Gold™ MiniFastFit (DJ/club)

Full EOC	871829122111100
Code de commande	287177
Numéro de matériau (12 N.C.)	928177105115
Numérateur – Quantité par emballage	1
EAN/CUP – Produit/Boîtier	8718291221111

Numérateur – Emballages par boîte extérieure	4
EAN/CUP – Boîte	8718291221128

Schéma dimensionnel



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold 300/2 MiniFastFit 1CT/4	23 mm	5,0 mm	65,8 mm	67,8 mm	66,8 mm	126 mm

