



MASTERColour CDM-TC 精锐型

MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12

单端、外型紧凑且高效的陶瓷金卤放电光源

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G8.5
操作位置	UNIVERSAL [任意或通用 (U)]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	20,000 小时
灯技术	
颜色代码	830 [CCT of 3000K]
光通量	1,750 lm
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.434
色度坐标 Y (标称)	0.398
相关色温 (标称)	3000 K
光效 (额定) (标称)	87 lm/W
显色指数 (CRI)	85


弧长 ϕ (标称)	4 mm
操作和电气	
功耗	20.1 W
电压 (标称)	95 V
电压 (标称)	95 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡材料	防紫外线石英
灯泡外形	T14 [T 14 毫米]

MASTERC colour CDM-TC 精锐型

审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	3.5 mg
汞 (Hg) 含量 (标称)	3.5 mg
能耗 kWh/1000 h	21 kWh
EPREL 注册号	473254
产品数据	
订单产品名称	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12
完整的产品名称	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12


完整产品代码	872790087158600
订购代码	928183405125
材料编号 (12NC)	928183405125
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8727900871586
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8727900871593

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	15 mm	0.55 in	4 mm	51 mm	53 mm	52 mm	85 mm

光度数据




Light Distribution Diagram - MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12



Spectral Power Distribution Colour - MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12

MASTERC colour CDM-TC 精锐型

寿命



Life Expectancy Diagram - MASTER CDM-TC Elite 20W/830 G8.5 1CT/12

Lumen Maintenance Diagram - MASTER CDM-TC Elite 20W/830 G8.5 1CT/12

