



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap base	PGJX28 [PGJX28]	Power (Rated) (Nom)	575 W
Operating position	UNIVERSAL [Any or Universal (U)]	Lamp current (nom.)	10.2 A
Main application	Entertainment	Ignition supply voltage (min.)	198 V
Life to 50% failures (nom.)	750 h	Chromaticity coordinate X (nom.)	296
System description	MiniFastFit	Chromaticity coordinate Y (nom.)	315
Colour Code	2	Correlated Colour Temperature (Nom)	7500 K
Luminous flux (min.)	34500 lm	Luminous efficacy (rated) (nom.)	63 lm/W
Luminous flux (nom.)	38600 lm	Colour rendering index (nom.)	70

MSR Gold™ MiniFastFit (Touring/Stage)

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-base information	PGJX28
----------------------	--------


Luminaire Design Requirements

Bulb temperature (max.)	950 °C
Pinch temperature (max.)	400 °C
Pinch temperature (min.)	300 °C

Product Data

Full product code	871829122109800
Order product name	MSR Gold™ 575/2 MiniFastFit 1CT/4
EAN/UPC – product	8718291221098
Order code	22109800
SAP numerator – quantity per pack	1
SAP numerator – packs per outer box	4
SAP material	928184005115
Net Weight (Piece)	0.070 kg



Dimensional drawing



MSR GOLD 575/2 MiniFastFit

Product	D (max)	O (max)	L (min)	L (max)	L (max)	C (max)	F (max)	F (max)	F (min)
MSR Gold™ 575/2 MiniFastFit 1CT/4	23.2 mm	3.5 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

Photometric data



XDPB_XDMSR_0004-Spectral power distribution B/W

MSR Gold™ MiniFastFit (Touring/Stage)

