



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

| General Information | | Colour Rendering Index,horiz (Nom) | |
|--------------------------------------|----------------------------|------------------------------------|--------|
| Cap base | PGJX28 [PGJX28] | | 70 |
| Burning Position | UNIVERSAL [Any/Universal] | Operating and Electrical | |
| Main application | Entertainment | Power (Rated) (Nom) | 575 W |
| Life to 50% failures (nom.) | 750 h | Lamp current (nom.) | 10.2 A |
| System description | MiniFastFit | Ignition supply voltage (min.) | 198 V |
| Light Technical | | Controls and Dimming | |
| Colour Code | 2 | Dimmable | yes |
| Lamp Luminous Flux 25°C EL (Min) | 34500 lm | Mechanical and Housing | |
| Lamp Luminous Flux 25°C EL (Nom) | 38600 lm | Cap base information | PGJX28 |
| Chromaticity coordinate X (nom.) | 296 | Luminaire Design Requirements | |
| Chromaticity coordinate Y (nom.) | 315 | Bulb temperature (max.) | 950 °C |
| Colour Temperature, horizontal (Nom) | 7500 K | Pinch temperature (max.) | 400 °C |
| Lamp Luminous Efficacy EM (Nom) | 63 lm/W | | |

MSR Gold™ MiniFastFit (Touring/Stage)


| | |
|--------------------------|-----------------------------------|
| Pinch temperature (min.) | 300 °C |
| Product Data | |
| Full product code | 871829122109800 |
| Order product name | MSR Gold™ 575/2 MiniFastFit 1CT/4 |
| EAN/UPC – product | 8718291221098 |
| Order code | 22109800 |

| | |
|---------------------------------|--------------|
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 4 |
| Material no. (12NC) | 928184005115 |
| Net weight (piece) | 0.070 kg |

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



Dimensional drawing



| Product | D (max) | O (min) | L (min) | L (max) | L (max) | C (max) | F (max) | F (min) | F (min) |
|-------------|------------|------------|------------|------------|------------|------------|------------|------------|------------|
| MSR Gold™ | 23.2 | 3.5 | 55 mm | 57 mm | 56 | 112 mm | 36.5 | 36 | 35.3 |
| 575/2 | mm | mm | | | | mm | mm | mm | mm |
| MiniFastFit | | | | | | | | | |
| 1CT/4 | | | | | | | | | |

MSR GOLD 575/2 MiniFastFit

Photometric data



MSR Gold™ MiniFastFit (Touring/Stage)

