



MSR Platinum (Touring/Stage)

MSR Platinum 35 1CT/16

Today's stage designs call for lighting solutions which deliver high brightness and high-contrast beams to avoid shadow creation, as well as more compact luminaire and fixture designs to improve creative choice and design flexibility. Addressing this need, we have developed an incredibly powerful, brilliant and lightweight, compact system for the most amazing light experience – MSR Platinum 35. This lamp system provides a powerful and innovative tool to create intense lighting and delivers the same good light quality as other MSR lamps. The exceptionally short arc generates sparkling, bright light and this ultra-compact design makes the lamp suitable for smaller stage lighting fixtures.

Mises en garde et sécurité

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Données du produit

Renseignements généraux	
Culot-Base	PGJX36 [PGJX36]
Position de fonctionnement	UNIVERSEL [Tous ou universel (U)]
Durée de vie jusqu'à 50% des défaillances (nom.)	1 000 h

Données techniques sur l'éclairage	
Code de couleur	2
Flux lumineux	57 800 lm
Coordonnée de chromaticité X (nominale)	0,295
Coordonnée de chromaticité Y (nominale)	0,313
Température de couleur proximale (nom.)	8500 K

Efficacité lumineuse (nominale)	72 lm/W
Indice de rendu des couleurs (IRC)	73
Longueur de l'arc O (nominal)	3,0 mm

Fonctionnement et électricité	
Consommation	800 W
Courant de la lampe (nom.)	12,0 A

Commandes et gradation	
Intensité variable	Oui


MSR Platinum (Touring/Stage)

Données de produit

Nom du produit de la commande	MSR Platinum 35 1CT
Nom complet du produit	MSR Platinum 35 1CT/16
Full EOC	871829112006300
Code de commande	245977
Numéro de matériau (12 N.C.)	928190905114


Numérateur – Quantité par emballage	1
EAN/CUP – Produit/Boîtier	8718291120063
Numérateur – Emballages par boîte extérieure	16
EAN/CUP – Boîte	8718291120070

Schéma dimensionnel



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Platinum 35 1CT	23,5 mm	3,0 mm	55 mm	57 mm	56 mm	116 mm

Données photométriques



Spectral Power Distribution Colour - MSR Platinum 35 1CT

