



MASTERColour CDM-T Elite

MASTERColour CDM-T Elite 50W/930 G12 1CT/12

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp

Product data

General Information	
Cap base	G12 [G12]
Operating position	UNIVERSAL [Any/Universal]
Life to 5% failures (nom.)	12000 h
Life to 10% failures (nom.)	14000 h
Life to 20% failures (nom.)	16000 h
Life to 50% failures (nom.)	20000 h
ANSI code HID	-
Light Technical	
Colour code	930 [CCT of 3,000 K]
Luminous flux (rated) (nom.)	5450 lm
Colour designation	Warm white (WW)
Lumen maintenance 1,000 hours (nom.)	97 %
Lumen maintenance 12,000 hours (nom.)	82 %
Lumen maintenance 10,000 hours (nom.)	83 %
Lumen maintenance 2,000 hours (nom.)	95 %
Lumen maintenance 4,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	88 %
Chromaticity coordinate X (nom.)	0.435
Chromaticity coordinate Y (nom.)	0.396
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	108 lm/W

Color rendering index (min.)	87
Color rendering index (nom.)	90
Operating and Electrical	
Power (Rated) (Min)	50.0 W
Power (Rated) (Nom)	50 W
Lamp current run-up (max.)	2 A
Ignition supply voltage (max.)	198 V
Ignition peak voltage (max.)	5000 V
Ignition supply voltage (min.)	198 V
Re-ignition time (min.) (max.)	15 min
Ignition time (max.)	30 s
Voltage (Max)	96 V
Voltage (Min)	84 V
Voltage (Nom)	90 V
Controls and Dimming	
Dimmable	no
Run-up time 90% (max.)	3 min
Mechanical and Housing	
Bulb finish	Clear (CL)

MASTERCcolour CDM-T Elite

Approval and Application

Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	6.6 mg
Energy Consumption kWh/1000 h	55 kWh

UV

PET (NIOSH) (min.)	8 h/500lx
Damage factor D/fc (max.)	0.3

Luminaire Design Requirements

Bulb temperature (max.)	500 °C
Cap base temperature (max.)	250 °C
Pinch temperature (max.)	350 °C


Product Data

Full product code	872790093060300
Order product name	MASTERCcolour CDM-T Elite 50W/930 G12 1CT/12
EAN/UPC – product	8727900930603
Order code	93060300
Local Code	50CDMTELITE930
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	928191705131
Net weight (piece)	0.030 kg
ILCOS Code	MT/UB-50/930-H-G12-20/90

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing




CDM-T Elite 50W/930 G12

Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERCcolour CDM-T Elite 50W/930 G12 1CT/12	20 mm	6 mm	55 mm	57 mm	56 mm	103 mm

MASTERC colour CDM-T Elite

Photometric data



Lifetime

