



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information		Color rendering index (nom.)	
Cap base	PGJX28 [PGJX28]		65
Operating position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Main application	Entertainment	Power (Rated) (Nom)	700 W
Life to 50% failures (nom.)	750 h	Lamp current (nom.)	10.8 A
System description	MiniFastFit	Ignition supply voltage (min.)	220 V
Light Technical		Controls and Dimming	
Colour code	- [Not Specified]	Dimmable	Yes
Luminous flux (min.)	44500 lm	Mechanical and Housing	
Luminous flux (nom.)	49000 lm	Cap base information	PGJX28
Chromaticity coordinate X (nom.)	289	Luminaire Design Requirements	
Chromaticity coordinate Y (nom.)	308	Bulb temperature (max.)	950 °C
Correlated colour temperature (nom.)	6000 K		
Luminous efficacy (rated) (nom.)	70 lm/W		

MSR Gold™ MiniFastFit (Touring/Stage)


Pinch temperature (max.)	450 °C
Product Data	
Full product code	871829114103700
Order product name	MSR Gold™ 700 MiniFastFit 1CT/16
EAN/UPC – product	8718291141037
Order code	14103700

Numerator – quantity per pack	1
Numerator – packs per outer box	16
Material no. (12NC)	928194105114
Net weight (piece)	0.053 kg

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



MSR GOLD 700 MiniFastFit

Product	D (max)	O (min)	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™ 700 MiniFastFit 1CT/16	23 mm	3.5 mm	55 mm	57 mm	56 mm	116 mm	36.5 mm	36 mm	35.3 mm

