



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold™ 700 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information			
Cap-Base	PGJX28 [PGJX28]	Luminous Efficacy (rated) (Nom)	70 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	72
Life to 50% Failures (Nom)	750 hour(s)	Arc Length O (Nom)	3.5 mm
Light Technical		Operating and Electrical	
Color Code	- [Not Specified]	Power Consumption	700 W
Luminous Flux	49,000 lm	Lamp Current (Nom)	10.8 A
Chromaticity Coordinate X (Nom)	289	Controls and Dimming	
Chromaticity Coordinate Y (Nom)	308	Dimmable	Yes
Correlated Color Temperature (Nom)	6000 K		

MSR Gold™ MiniFastFit (Touring/Stage)

Product Data	
Order product name	MSR Gold 700 MiniFastFit 1CT/16
Full product name	MSR Gold™ 700 MiniFastFit 1CT/16
Full product code	871829114103700
Order code	14103700
Material Nr. (12NC)	928194105114

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291141037
Numerator - Packs per outer box	16
EAN/UPC - Case	8718291141044

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 700 MiniFastFit 1CT/16	23 mm	3.5 mm	55 mm	57 mm	56 mm	116 mm	36.5 mm	36 mm	35.3 mm

