



MASTERColour CDM-R111 Elite

MASTERC CDM-R111 Elite 35W/930 GX8.5 24D

MASTERColour CDM-R111 Elite combines the trendy look of 111 mm aluminium-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/930 lamps may also use electromagnetic gear.
- Use only with electronic control gear. 35W/930 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information			
Cap-Base	GX8.5 [GX8.5]	Luminous Flux	1,750 lm
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Intensity (Nom)	8,500 cd
Switching Cycle	1,050	Color Designation	Warm White (WW)
Flux measurement reference	Narrow Cone	Chromaticity Coordinate X (Nom)	0.434
Life to 50% Failures (Nom)	12,000 hour(s)	Chromaticity Coordinate Y (Nom)	0.398
		Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	46 lm/W
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	930 [CCT of 3000K]		
Beam Angle (Nom)	24 degree(s)		

MASTERC colour CDM-R111 Elite

Luminous Flux in 90° Cone (Rated)	1,750 lm
Operating and Electrical	
Power Consumption	39.1 W
Warm-up time to 60% light	120 s
Voltage (Nom)	89 V
Voltage (Nom)	89 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Reflector
Bulb Shape	R111 [R 111mm]
Approval and Application	
Energy Efficiency Class	G


Mercury (Hg) Content (Max)	4.7 mg
Mercury (Hg) Content (Nom)	4.7 mg
Energy Consumption kWh/1000 h	40 kWh
EPREL Registration Number	473280
Product Data	
Order product name	MASTERC CDM-R111 Elite 35W/930 GX8.5 24D
Full product name	MASTERC CDM-R111 Elite 35W/930 GX8.5 24D
Full product code	871829168944700
Order code	928195405330
Material Nr. (12NC)	928195405330
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291689447
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291689454

Dimensional drawing



Product	D (max)	C (max)
MASTERC CDM-R111 Elite 35W/930 GX8.5 24D	111 mm	95 mm

Photometric data



Spectral Power Distribution Colour - MASTERC CDM-R111 Elite 35W/930 GX8.5 24D

115°/160°/150°

Light Distribution Diagram - MASTERC CDM-R111 Elite 35W/930 GX8.5 24D

MASTERColour CDM-R111 Elite

