



MasterColor CDM-R111 Elite

MASTERColor CDM-R111 Elite 35W/930 GX8.5 40D

MasterColor CDM-R111 Elite combines the trendy look of 111 mm aluminum-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MasterColor CDM.

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/930 lamps may also use electromagnetic gear
- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	GX8.5 [GX8.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Switching Cycle	1,050
Life to 50% Failures (Nom)	12,000 hour(s)
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 degree(s)


Luminous Intensity (Nom)	4,500 cd
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.432
Chromaticity Coordinate Y (Nom)	0.392
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	46 lm/W
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

MasterColor CDM-R111 Elite

Luminous Flux in 90° Cone (Rated)	1,750 lm
Operating and Electrical	
Power Consumption	39 W
Warm-up time to 60% light	120 s
Voltage (Nom)	89 V
Voltage (Nom)	89 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Reflector
Bulb Shape	R111 [R 111mm]
Approval and Application	
Mercury (Hg) Content (Nom)	4.7 mg


Energy Consumption kWh/1000 h	43 kWh
Product Data	
Order product name	MASTERC CDM-R111 Elite 35W/930 GX8.5 40D
Full product name	MASTERCOLOR CDM-R111 Elite 35W/930 GX8.5 40D
Order code	430744
Material Nr. (12NC)	928195505306
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677430740
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677430745

Dimensional drawing




Product	D (max)	C (max)
MASTERC CDM-R111 Elite 35W/930 GX8.5 40D	111 mm	95 mm

Photometric data



Spectral Power Distribution Colour - MASTERC CDM-R111 Elite 35W/930 GX8.5 40D



Light Distribution Diagram - MASTERC CDM-R111 Elite 35W/930 GX8.5 40D

MasterColor CDM-R111 Elite

