



# MASTERColour CDM-R111 Elite

## MASTERColour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D

MASTERColour CDM-R111 Elite combines the trendy look of 111 mm aluminium-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

### Product data

General Information	
Cap base	GX8.5 [ GX8.5]
Operating position	UNIVERSAL [ Any/Universal]
Life to 5% failures (nom.)	8000 h
Life to 10% failures (nom.)	9500 h
Life to 20% failures (nom.)	10500 h
Life to 50% failures (nom.)	12000 h
ANSI code HID	-
Switching cycle	1050X
Light Technical	
Colour code	930 [ CCT of 3.000 K]
Beam Angle (Nom)	40 °
Beam angle technical	36 °
Beam angle technical	45 °
Beam angle technical	27 °
Luminous intensity (min.)	6500 cd
Luminous intensity (nom.)	8500 cd
Beam description	Flood [ Flood]
Colour designation	Warm white (WW)

Lumen maintenance 12,000 hours (nom.)	70 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 4,000 hours (nom.)	85 %
Design mean lumens	3100 lm
Chromaticity coordinate X (nom.)	0.441
Chromaticity coordinate Y (nom.)	0.397
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	50 lm/W
Color rendering index (min.)	89
Color rendering index (nom.)	92
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	3550 lm
Operating and Electrical	
Power (Rated) (Nom)	73.0 W
Re-ignition time (min.) (max.)	15 min
Warm-up time to 60% light (nom.)	120 s
Ignition time (max.)	30 s
Voltage (Max)	98 V
Voltage (Min)	80 V

# MASTERCcolour CDM-R111 Elite


Voltage (Nom)	89 V
<b>Controls and Dimming</b>	
Dimmable	no
Run-up time 90% (max.)	3 min
<b>Mechanical and Housing</b>	
Bulb finish	Reflector
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	6.6 mg
Energy Consumption kWh/1000 h	80 kWh

<b>Product Data</b>	
Full product code	871829168978200
Order product name	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D
EAN/UPC – product	8718291689782
Order code	68978200
Local Code	70CDMER11193040
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	928195805330
Net weight (piece)	96.000 g
ILCOS Code	MRS/UB-70/930-H-GX8.5-111/88/40

## Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/930 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



## Dimensional drawing



CDM-R111 Elite 70W/930 40D

Product	D (max)	C (max)
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 70W/930 GX8.5 40D	111 mm	95 mm

## Photometric data



## MASTERCcolour CDM-R111 Elite

