



MSD Platinum (Touring/Stage)

MSD Platinum 20 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Mises en garde et sécurité

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Données du produit

Renseignements généraux	
Culot-Base	- [-]
Position de fonctionnement	UNIVERSEL [Tous ou universel (U)]
Durée de vie jusqu'à 50% des défaillances (nom.)	1 500 h
Données techniques sur l'éclairage	
Code de couleur	2
Flux lumineux	22 400 lm
Coordonnée de chromaticité X (nominale)	296
Coordonnée de chromaticité Y (nominale)	298
Température de couleur proximale (nom.)	8000 K
Efficacité lumineuse (nominale)	47 lm/W
Indice de rendu des couleurs (IRC)	-


Longueur de l'arc O (nominal)	1,2 mm
Fonctionnement et électricité	
Consommation	470 W
Commandes et gradation	
Intensité variable	Oui
Données de produit	
Nom du produit de la commande	MSD Platinum 20 R 1CT/8
Nom complet du produit	MSD Platinum 20 R 1CT/8
Full EOC	871869647812700
Code de commande	259184

MSD Platinum (Touring/Stage)

Numéro de matériau (12 N.C.)	928197205314
Numérateur – Quantité par emballage	1
EAN/CUP – Produit/Boîtier	8718696478127
Numérateur – Emballages par boîte extérieure	8


EAN/CUP – Boîte	8718696478134
-----------------	---------------

Schéma dimensionnel



Product	D (max)	O	C (max)
MSD Platinum 20 R 1CT/8	58,5 mm	1,2 mm	72 mm

Données photométriques



Spectral Power Distribution Colour - MSD Platinum 20 R 1CT/8

