



MSD Platinum

MSD Platinum 2 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	- [-]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	6,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux	5,150 lm
Chromaticity Coordinate X (Nom)	289
Chromaticity Coordinate Y (Nom)	294
Correlated Color Temperature (Nom)	8000 K
Color rendering index (CRI)	-


Arc Length O (Nom)	1.2 mm
Operating and Electrical	
Power Consumption	132 W
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSD Platinum 2 R 1CT/8
Full product name	MSD Platinum 2 R 1CT/8
Full product code	871829173554000

MSD Platinum

Order code	928197605314
Material Nr. (12NC)	928197605314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291735540


Numerator - Packs per outer box	8
EAN/UPC - Case	8718291735557

Dimensional drawing



Product	D (max)	T (max)	O	C (max)
MSD Platinum 2 R 1CT/8	46.5 mm	13.5 mm	1.2 mm	57.1 mm

Photometric data



Spectral Power Distribution Colour - MSD Platinum 2 R 1CT/8

