



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information		Color Rendering Index (Nom)	
Base	PGJX28 [PGJX28]		75
Operating Position	Universal [Universal]	Operating and Electrical	
Main Application	Entertainment	Power (Rated) (Nom)	700 W
Life to 50% Failures (Nom)	750 h	Lamp Current (Nom)	10.2 A
System Description	MiniFastFit	Ignition Supply Voltage (Min)	198 V
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	Yes
Initial lumen (Min)	44000 lm	Mechanical and Housing	
Initial lumen (Nom)	47000 lm	Cap-Base Information	PGJX28
Chromaticity Coordinate X (Nom)	300	Luminaire Design Requirements	
Chromaticity Coordinate Y (Nom)	324	Bulb Temperature (Max)	950 °C
Correlated Color Temperature (Nom)	7200 K		
Luminous Efficacy (rated) (Nom)	69 lm/W		

MSR Gold™ MiniFastFit (Touring/Stage)


Pinch Temperature (Max)	500 °C
Product Data	
Order product name	MSR Gold™ 700/2 MiniFastFit 1CT/4
EAN/UPC - Product	8718291221173
Order code	286922

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928199905115
Net Weight (Piece)	0.052 kg

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



Product	D (max)	O (min)	L (min)	L (max)	L (max)	C (max)	F (max)	F (min)	F (min)
MSR Gold™ 700/2 MiniFastFit	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

MSR GOLD 700/2 MiniFastFit

Photometric data



MSR Gold™ 575/2 MiniFastFit, MSR Gold™ 700/2 MiniFastFit

MSR Gold™ 575/2 MiniFastFit, MSR Gold™ 700/2 MiniFastFit

MSR Gold™ MiniFastFit (Touring/Stage)

