



Starters for tanning lamps

S12 STARTER 500 PK

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

Product data


General Information		Cap-Base Information	
System Description	Single	Cap-Base Information	2P
Operating and Electrical		Product Data	
Power (Rated) (Nom)	115-140 W	Order product name	S12 115-140W 220-240V UNP/20X25CT
Pulse Voltage (Min)	600 V	EAN/UPC - Product	8711500903792
Non Reclosure Voltage (Min)	135 V	Order code	246991
Voltage (Nom)	220-240 V	Numerator - Quantity Per Pack	1
System characteristics		Numerator - Packs per outer box	500
Capacitor	Yes	Material Nr. (12NC)	928391630303
Mechanical and Housing		Net Weight (Piece)	7.000 g
Housing Color	Black		

Warnings and Safety

- Flame-retardant components
- UV-resistant canister

Starters for tanning lamps

Dimensional drawing



S12 115-140W SIN 220-240V BK

Product	C (max)	E (max)
S12 115-140W 220-240V UNP/20X25CT	40.3 mm	21.5 mm

