



MSR Gold™ FastFit

MSR Gold™ 2000/1 FastFit

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

| General Information | |
|------------------------------------|------------------------|
| Base | PGJX50 [PGJX50] |
| Operating Position | Universal [Universal] |
| Main Application | Entertainment |
| Life to 50% Failures (Nom) | 750 h |
| Light Technical | |
| Initial lumen (Min) | 155000 lm |
| Initial lumen (Nom) | 172000 lm |
| Chromaticity Coordinate X (Nom) | 329 |
| Chromaticity Coordinate Y (Nom) | 333 |
| Correlated Color Temperature (Nom) | 5700 K |
| Luminous Efficacy (rated) (Nom) | 86 lm/W |
| Color Rendering Index (Nom) | 90 |
| Operating and Electrical | |
| Power (Rated) (Nom) | 2000 W |

| Lamp Current (Nom) | 18.2 A |
|-------------------------------|--------------------------------|
| Ignition Supply Voltage (Max) | 198 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Cap-Base Information | PGJX50 |
| Luminaire Design Requirements | |
| Bulb Temperature (Max) | 950 °C |
| Pinch Temperature (Max) | 500 °C |
| Product Data | |
| Order product name | MSR Gold™ 2000/1 FastFit 1CT/8 |
| EAN/UPC - Product | 8718696679449 |
| Order code | 323709 |

MSR Gold™ FastFit


| | |
|---------------------------------|--------------|
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 8 |
| Material Nr. (12NC) | 928410105114 |

| | |
|--------------------|-----------|
| Net Weight (Piece) | 138.000 g |
|--------------------|-----------|

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing



| Product | D (max) | O | L (min) | L | L | C (max) | F |
|------------------|---------|------|---------|-------|-------|---------|-------|
| MSR Gold™ 2000/1 | 34 mm | 8 mm | 66 mm | 68 mm | 67 mm | 134 mm | 50 mm |
| FastFit 1CT/8 | | | | | | | |

MSR Gold 2000/1 FastFit

