



# Other digital cinema projectors

## XDC 6500 TA


Digital Xenon Cinema TA-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. There is a choice of four power ratings in the TA-type Digital Cinema Xenon lamps range: 3000W, 4500W, 6000W or 6500W. These lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to TA-type Digital Cinema Xenon lamps there are B-, C-, N-, and S-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

### Product data

<b>General Information</b>		<b>Order product name</b>	XDC 6500 TA
<b>Operating Position</b>	P15 [Parallel +/-15D or Horizontal(HOR)]	<b>Order code</b>	928414606301
<b>Nominal lifetime</b>	500 hour(s)	<b>Numerator - Quantity Per Pack</b>	1
<b>Operating and Electrical</b>		<b>Numerator - Packs per outer box</b>	1
<b>Power Consumption</b>	6,500 W	<b>Material Nr. (12NC)</b>	928414606301
<b>Lamp Current (Nom)</b>	170 A	<b>Full product name</b>	XDC 6500 TA
<b>Voltage (Nom)</b>	38 V	<b>EAN/UPC - Case</b>	8727900856293
<b>Voltage (Nom)</b>	38 V	<b>EAN/UPC - Product/Case</b>	8727900856293
<b>Product Data</b>			
<b>Full product code</b>	872790085629300		

Other digital cinema projectors

Dimensional drawing



Product	O	D	X	B (max)	C (max)	A
XDC 6500 TA	7.5 mm	70 mm	400 mm	391 mm	433 mm	170.5 mm

