



Barco digital cinema projectors

XDC 3001 B


Digital Xenon Cinema B-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for Barco projectors. There is a choice of three power ratings in the B-type Digital Xenon Cinema lamps range: 3000W, 4000W, or 6500W. There is also a choice of three power ratings in the BH-type Digital Helios lamps: 2000W, 3000W, and 4200W power ratings. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to B-type Digital Cinema Xenon lamps there are C-, N-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

Product data

General Information			
Operating Position	P15 [Parallel +/-15D or Horizontal(HOR)]	Order product name	XDC 3001 B
Nominal lifetime	1,500 hour(s)	Order code	928417806301
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	3,001 W	Numerator - Packs per outer box	1
Lamp Current (Nom)	110 A	Material Nr. (12NC)	928417806301
Voltage (Nom)	29 V	Full product name	XDC 3001 B
Voltage (Nom)	29 V	EAN/UPC - Case	8718291249672
Product Data		EAN/UPC - Product/Case	8718291249672
Full product code	871829124967200		

Dimensional drawing

Product	O	D	X	B (max)	C (max)	A
XDC 3001 B	5.0 mm	55 mm	152 mm	302 mm	342 mm	145 mm



Product
XDC 3001 B

