



MASTER HPI-T Plus

MASTER HPI-T Plus 400W/645 E40 1SL/12

带透明外部灯泡的石英金属卤化物灯

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	E40 [E40]
操作位置	P20 [并行 +/-20D 或水平 (HOR)]
50% 故障条件下的使用寿命 (标称)	20,000 小时
灯技术	
颜色代码	645 [CCT of 4500K]
颜色名称	冷白色 (CW)
色度坐标 X (标称)	361
色度坐标 Y (标称)	372
相关色温 (标称)	4500 K
光效 (额定) (标称)	83 lm/W
显色指数 (CRI)	65
弧长 O (标称)	30.5 mm
操作和电气	
功耗	385 W
电压 (标称)	125 V


电压 (标称)	125 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡外形	T46 [T 46 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	29.5 mg
能耗 kWh/1000 h	424 kWh
产品数据	
订单产品名称	MASTER HPI-T Plus 400W/645 E40 1SL/12
完整的产品名称	MASTER HPI-T Plus 400W/645 E40 1SL/12
完整产品代码	692234199963500
订购代码	928481600094

MASTER HPI-T Plus

材料编号 (12NC)	928481600094
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6922341999635
计算器 - 每个外包装箱中的包数	12



EAN/UPC - 案例	6922341993244
--------------	---------------

二维绘图



Product	D (max)	O	L	C (max)
MASTER HPI-T Plus 400W/645 E40 1SL/12	47 mm	30.5 mm	168 mm	286 mm



光度数据



Light Distribution Diagram - MASTER HPI-T Plus 400W/645 E40 1SL/12

Spectral Power Distribution Colour - MASTER HPI-T Plus 400W/645 E40 1SL/12

寿命



Life Expectancy Diagram - MASTER HPI-T Plus 400W/645 E40 1SL/12

Lumen Maintenance Diagram - MASTER HPI-T Plus 400W/645 E40 1SL/12

MASTER HPI-T Plus

