

# PHILIPS

# Lighting



## HPI-T

### HPI-T 1000W/543 E40 1SL/4

Quartz metal halide lamps with clear outer bulb

#### Product data

General Information	
Cap base	E40 [ E40]
Burning Position	P [ Parallel or Horizontal(HOR)]
Life to 5% failures (nom.)	3000 h
Life to 10% failures (nom.)	5500 h
Life to 20% failures (nom.)	8000 h
Life to 50% failures (nom.)	12000 h
System description	na [-]

Light Technical	
Colour Code	543 [ CCT of 4,300 K]
Lamp Luminous Flux (Min)	79000 lm
Lamp Luminous Flux (Nom)	85000 lm
Colour Designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	87 %
Lumen maintenance 5,000 hours (nom.)	80 %
Chromaticity coordinate X (nom.)	370
Chromaticity coordinate Y (nom.)	380
Colour Temperature, horizontal (Nom)	4300 K
Lamp Luminous Efficacy EM (Nom)	86 lm/W
Colour Rendering Index,horiz (Nom)	57

Operating and Electrical	
Lamp supply voltage	220 V [ 220]
Power (Rated) (Nom)	985.0 W

Controls and Dimming	
Dimmable	no

Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	86 mg
Energy Consumption kWh/1000 h	1084 kWh

Luminaire Design Requirements	
Bulb temperature (max.)	555 °C
Cap base temperature (max.)	300 °C

Product Data	
Full product code	871150018373645

# HPI-T


Order product name	HPI-T 1000W/543 E40 1SL/4
EAN/UPC – product	8711500183736
Order code	928482600096
Numerator – quantity per pack	1
Numerator – packs per outer box	4

Material no. (12NC)	928482600096
Net weight (piece)	0.426 kg

## Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing



Product	D (max)	O	L	C (max)
HPI-T 1000W/543 E40 1SL/4	66 mm	80 mm	240 mm	382 mm

HPI-T 1000W/543 E40

## Photometric data



# HPI-T

## Lifetime

